



CoreLine Panel gen6

RC132V G6 36S/UE840 PSD W60L60 OC

CoreLine Panel gen6, UltraEfficient, 23.5 W, 600x600 mm, VPC, 3600 lm, 4000 K, DALI, UGR19

600x600 mm, Visible profile ceiling version, Steel, White, Signal white (RAL9003), Power supply unit with DALI interface, 3600 lm, 23.5 W, 153 lm/W, 4000 K, (0.38, 0.38) SDCM \leq 3, UGR19, Beam angle 90°, Microprismatic lens, Polystyrene, IP20/44 | Finger-protected; wire-protected, splash-proof, IK02 | 0.2 J standard, Safety class II, Push-in connector 4-pole, SC | Safety cable

Product data

General Information		Operating and Electrical	
Number of gear units	Unit	Input Voltage	220 to 240 V
Driver included	Yes	Line Frequency	50 or 60 Hz
Service Tag	Yes	Inrush current	25.2 A
Value ladder	Performance	Inrush time	0.26 ms
Warranty period	5 years	Power Consumption	23.5 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	3,600 lm	Connection	Push-in connector 4-pole
Correlated Colour Temperature (Nom)	4000 K	Cable	-
Luminous efficacy (rated) (nom.)	153 lm/W	Number of products on MCB (16 A type B)	11
Colour rendering index (CRI)	>80	Suitable for random switching	Not applicable
Beam angle of light source	90 degree(s)	Protection class IEC	Safety class II
Light source colour	840 neutral white	Total harmonic distortion	20 %
Optic type	Beam angle 90°	Controls and Dimming	
Luminaire light beam spread	90°	Dimmable	Yes
Unified Glare Rating (CEN)	19	Driver/power unit/transformer	Power supply unit with DALI interface
		Control interface	DALI

CoreLine Panel gen6

Constant light output	No
DALI standard	DALI-2™
Maximum dim level	1%

Mechanical and Housing

Housing material	Steel
Reflector material	Acrylate
Optic material	Polystyrene
Optical cover/lens material	Polystyrene
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Microprismatic lens
Overall length	595 mm
Overall width	595 mm
Overall height	63 mm
Dimensions (height x width x depth)	63 x 595 x 595 mm
Compatible ceiling or ceiling installation accessory type	Visible profile ceiling version
Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Safety device	SC [Safety cable]
Net Weight (Piece)	2.250 kg

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Initial chromaticity	(0.38, 0.38) SDCM ≤3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at L90 median useful life* 50000 h	
Lumen maintenance (EN-IEC 62722-2-1) at L80 median useful life* 100000 h	

Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	24.6 kg CO ₂ e
Product non-virgin material ratio	10.1 %
Recyclable the content ratio of the finished product	47.9 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kwh)

Product Data

Order product name	RC132V G6 36S/UE840 PSD W60L60 OC
Full product name	RC132V G6 36S/UE840 PSD W60L60 OC
Full EOC	872016974983299
Order code	911401800287
Material no. (12 NC)	911401800287
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169749832
Numerator – packs per outer box	4
EAN/UPC – Case	8720169750098

CoreLine Panel gen6

Dimensional drawing



Photometric data



Polar Normal (separate) - 911401800287

