



CoreLine FastSet, surface-mounted

SM155C 26S/830_840 WIA TW3 PI5 L602

CoreLine FastSet, surface-mounted, All-in, 20.5 W, L602 mm, 2600 lm, 3000 K, 4000 K, Wireless, Interact Ready

L602 mm, Steel, White, Signal white (RAL9003), Wireless driver Interact System-ready, All-in, Multi Color Temperature, 2600 lm, 20.5 W, 130 lm/W, 3000 K, 4000 K, (0.38,0.38)SDCM<3;(0.44,0.40)SDCM<3, Opal, Opal, Polycarbonate, IP20/44 | Finger-protected; wire-protected, splash-proof, IK06 | 1 J, Safety class I, Push-in connector 5-pole, Feed-through wiring 3-phase

Product data

General Information		Unified Glare Rating (CEN)	
Number of gear units	Unit	Unified Glare Rating (CEN)	25
Driver included	Yes	All-in Type	All-in, Multi Color Temperature
Service Tag	Yes	Operating and Electrical	
Value ladder	Performance	Input Voltage	220 to 240 V
Warranty period	5 years	Line Frequency	50 or 60 Hz
Light Technical		Inrush current	19 A
Luminous Flux	2,600 lm	Inrush time	0.23 ms
Saturated Red (R9)	<50	Power Consumption	20.5 W
Correlated Colour Temperature (Nom)	3000 4000 K	Power Factor (Fraction)	0.9
Luminous efficacy (rated) (nom.)	130 lm/W	Connection	Push-in connector 5-pole
Colour rendering index (CRI)	>80	Cable	-
Light source colour	-	Number of products on MCB (16 A type B)	24
Optic type	Opal	Suitable for random switching	Yes
Luminaire light beam spread	110°	Protection class IEC	Safety class I
		Feed-through wiring	Feed-through wiring 3-phase

CoreLine FastSet, surface-mounted

Total harmonic distortion	20 %
---------------------------	------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Wireless driver Interact System-ready
Control interface	Wireless
Constant light output	No
Maximum dim level	1%
Connectivity	Interact Ready

Mechanical and Housing

Housing material	Steel
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	602 mm
Overall width	163 mm
Overall height	67 mm
Dimensions (height x width x depth)	67 x 163 x 602 mm
Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK06 [1 J]
Net Weight (Piece)	1.600 kg

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM)	0.5
Stroboscopic effect	0.5
Ambient temperature range	-20°C to 45°C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<3;(0.44,0.40)SDCM<3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L65

Sustainability Data



Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	48.2 kg CO _{2e}
Product non-virgin material ratio	0.0137 %
Recyclable the content ratio of the finished product	0.0408 %
GWP total B6 (kg CO _{2eq}) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO _{2eq} / kWh)
GWP total B6 (kg CO _{2eq}) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kWh)

Product Data


Order product name	SM155C 26S/830_840 WIA TW3 PI5 L602
Full product name	SM155C 26S/830_840 WIA TW3 PI5 L602
Full EOC	872016975072299
Order code	911401803487
Material no. (12 NC)	911401803487
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169750722
Numerator – packs per outer box	4
EAN/UPC - Case	8720169750777

CoreLine FastSet, surface-mounted

Dimensional drawing



Photometric data



Polar Normal (separate) - 911401803487

