



CoreLine Waterproof

WT120C G2 LED40S/840 PSU L1200

CoreLine Waterproof, 28.6 W, L1200 mm, 4000 lm, 4000 K, Wide beam, Matte, IP65, IK08, TW1-ready

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch. Also available as an Interact Ready wireless CoreLine waterproof luminaire that works with Interact Pro lighting software and Interact Ready devices to provide a connected lighting system for SMEs

Warnings and Safety

- UV radiation will damage the material over time, resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

General Information		Operating and Electrical	
Light source replaceable	No	Correlated Colour Temperature (Nom)	4000 K
Number of gear units	Unit	Luminous efficacy (rated) (nom.)	140 lm/W
Driver included	Yes	Colour rendering index (CRI)	>80
Service Tag	Yes	Light source colour	840 neutral white
Lighting Technology	LED	Optic type	Wide beam
Value ladder	Performance	Luminaire light beam spread	105°
Warranty period	5 years	Unified Glare Rating (CEN)	25
Light Technical		Input Voltage	220 to 240 V
Luminous Flux	4,000 lm	Line Frequency	50 or 60 Hz

CoreLine Waterproof

Inrush current	14.2 A
Inrush time	0.222 ms
Power Consumption	28.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB (16 A type B)	36
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
Total harmonic distortion	20 %

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Grey
Optical cover/lens finish	Matte
Overall length	1,215 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (height x width x depth)	76 x 80 x 1215 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	1.260 kg

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	* – According to the Lighting Europe guidance paper 'Evaluating the performance of LED - based luminaires – January 2018; statistically there is no relevant difference in lumen maintenance between the B50 and, for

Flickering value (PstLM)	1
Stroboscopic effect	1.6
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L70

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	9.43 kg CO ₂ e
Product non-virgin material ratio	10.7 %
Recyclable the content ratio of the finished product	53.9 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kWh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kWh)


Product Data

Order product name	WT120C G2 LED40S/840 PSU L1200
Full product name	WT120C G2 LED40S/840 PSU L1200
Full EOC	871829184048099
Order code	911401823780
Material no. (12 NC)	911401823780
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291840480
Numerator – packs per outer box	9
EAN/UPC - Case	8710163346342


CoreLine Waterproof

Product family code WT130C [Coreline Waterproof G2 LSC]

Dimensional drawing



Photometric data



Polar Normal (separate) - WT120CI - 911401823780

