



Infrared Lamps Industrial Use

R125 IR 375W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data


General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 hour(s)
Rated Lifetime (Hours)	5,000 hour(s)
Lighting Technology	Incandescent
Operating and Electrical	
Power Consumption	375 W
Voltage (Nom)	230-250 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	R125
Net Weight (Piece)	0.302 lb
Approval and Application	
CE mark	Yes
Product Data	
Order product name	R125 IR 375W E27 230-250V CL 1CT/10
Full product name	R125 IR 375W E27 230-250V CL 1CT/10
Full product code	871150012659725
Order code	250472
Material Nr. (12NC)	923223543807
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500126597
Numerator - Packs per outer box	10

Infrared Lamps Industrial Use

EAN/UPC - Case	8711500141118
----------------	---------------

Dimensional drawing



Product	D	C (max)
R125 IR 375W E27 230-250V CL 1CT/10	4-15/16 inch	7-1/4 inch

