



PAR38

120 W E27 cap Clear Incandescent reflector bulb

Pressed-glass 121 mm diameter reflector lamps of high luminous intensity


Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	10 degree(s)
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	1,545 lm
Operating and Electrical	
Power Consumption	120.0 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	24 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	PAR38
Approval and Application	
Energy Consumption kWh/1000 h	127 kWh
Product Data	
Order product name	120 W E27 cap Clear Incandescent reflector bulb
Full product name	120 W E27 cap Clear Incandescent reflector bulb
Full product code	871150038073915
Order code	923810020511
Material Nr. (12NC)	923810020511
Numerator - Quantity Per Pack	1
Net Weight (Piece)	319.000 g
EAN/UPC - Product/Case	8711500380739
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500381118


PAR38

Dimensional drawing



Product	D (max)	C (max)	C1
120 W E27 cap Clear Incandescent reflector bulb	123 mm	137 mm	123 mm

Photometric data



Light Distribution Diagram - PAR38 120W E27 24V SP 10D 1CT/12

