

Appliance Refrigerator Tubular

15 W E14 cap Incandescent appliance bulb

Tubular lamp with clear glass bulb

Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	110 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	15.0 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230-240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T25
Net Weight (Piece)	12.500 g


Approval and Application	
Energy Consumption kWh/1000 h	15 kWh

Product Data	
Order product name	15 W E14 cap Incandescent appliance bulb
Full product name	15 W E14 cap Incandescent appliance bulb
Full product code	871150003851750
Order code	924197744440
Material Nr. (12NC)	924197744440
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500038517
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500250827

Appliance Refrigerator Tubular

Dimensional drawing

Product	D (max)	C (max)
15 W E14 cap Incandescent appliance bulb	25 mm	57 mm



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.