



# HalogenA PAR30S

## HalogenA Par30s 75W E27 230V 25D 1CT/15

Mains-voltage 97 mm diameter reflector lamp


### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	30 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	725 lm
Operating and Electrical	
Power Consumption	75.0 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
Approval and Application	
Energy Consumption kWh/1000 h	75 kWh
Product Data	
Order product name	HalogenA Par30s 75W E27 230V 25D 1CT/15
Full product name	HalogenA Par30s 75W E27 230V 25D 1CT/15
Full product code	871150088701600
Order code	924710844281
Material Nr. (12NC)	924710844281
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500887016
Numerator - Packs per outer box	15
EAN/UPC - Case	8711500887030


# HalogenA PAR30S

## Dimensional drawing



Product	D (max)	C (max)
HalogenA Par30s 75W E27 230V 25D 1CT/15	96 mm	99 mm

## Photometric data



Light Distribution Diagram - HalogenA Par30s 75W E27 230V 25D 1CT/15

