

LIGHTOLIER

by @signify

Track Lighting

Par-Tech

8215WH Cone 16 Shade

Project:

Location:


Cat.No:

Type:


Lamps:

Qty:


Notes:



CONE 16 WITH LOW PROFILE ADAPTER



CONE 16 WITH HINGED ADAPTER



Ordering Information

Catalog No.	Finishes	Mounting	Lamps
8215WH 8215BK	Matte White Matte Black	All Lytespan Track Systems	75W PAR16 (Tungsten-Halogen) (60W Max. with Accessories)

Features

- Shade Attachment:** Zinc plated and painted C.R. steel. Bayonet fitting.
- Shade:** Single piece die-cast aluminum.
- Mounting Groove:** For accessory holder.
- Color Accent Ring:** Silicone rubber. (Removable)
- Perimeter Venting**

Options & Accessories

2" Beam Smoother and Beam Elongator. All require Accessory Holder 8581. See Lightolier Specification Sheets, AF2LF and AF2AS.
Do not use with AL2HC louver.

Finish

All painted finishes baked enamel.

Labels

UL; I.B.E.W.

8215WH Par-Tech

Cone 16 Shade


Lighting Data

Aiming Angle


L Beam Length
W Beam Width
C Distance to center beam
D Distance
A Aiming Angle
FC Footcandles

L and **W** are the outer points where the candle power drops to 50% of the maximum. **FC** are the initial footcandles at the center of the beam.


0°



30°, 45° or 60° Horizontal



30°, 45° or 60° Vertical



LAMP

	Beam Spread 50% Max. CP	Beam Center C.P. Candelas	Rated Life-Hrs	0°				30°				45°				60°						
				D	FC	L	W	D	C	FC	L	W	D	C	FC	L	W	D	C	FC	L	W
 60W PAR16 NSP (Halogen)		5,000	2,000	6'	139	1.0'	1.0'	5'	2.9'	130	1.2'	1.0'	3'	3.0'	196	1.1'	0.7'	2'	3.5'	156	1.4'	0.7'
				8'	78	1.4'	1.4'	7'	4.0'	65	1.6'	1.4'	5'	5.0'	71	1.6'	1.2'	3'	5.2'	69	2.1'	1.0'
				10'	50	1.7'	1.7'	9'	5.2'	40	2.1'	1.8'	7'	7.0'	36	2.5'	1.7'	4'	6.9'	39	2.9'	1.4'
				12'	35	2.1'	2.1'	11'	8.4'	27	2.8'	2.2'	9'	9.0'	22	3.2'	2.2'	5'	8.7'	25	3.6'	1.7'
 60W PAR16 NFL (Halogen)		1,300	2,000	3'	144	1.6'	1.6'	3'	1.7'	94	2.2'	1.0'	2'	2.0'	115	2.3'	1.5'	1'	1.7'	163	2.7'	1.1'
				5'	52	2.7'	2.7'	5'	2.9'	34	3.7'	3.1'	3'	3.0'	51	3.5'	2.3'	2'	3.5'	41	5.5'	2.1'
				7'	27	3.6'	3.8'	7'	4.0'	17	5.1'	4.3'	4'	4.0'	29	4.6'	3.0'	3'	5.2'	18	6.2'	3.2'
				9'	16	4.8'	4.8'	9'	5.2'	10	6.6'	5.6'	5'	5.0'	18	5.8'	3.8'	4'	6.9'	10	10.8'	4.3'
 75W PAR16 (Halogen)		7,500	2,000	7'	153	1.2'	1.2'	6'	3.5'	135	1.4'	1.2'	4'	4.0'	166	1.4'	1.0'	2'	3.5'	234	1.4'	0.7'
				10'	75	1.7'	1.7'	9'	5.2'	60	2.1'	1.8'	6'	6.0'	74	2.1'	1.5'	3'	5.2'	104	2.1'	1.0'
				13'	44	2.3'	2.3'	12'	6.9'	34	2.8'	2.4'	9'	9.0'	41	2.8'	2.0'	4'	6.9'	59	2.9'	1.4'
				16'	29	2.8'	2.8'	13'	8.7'	22	3.5'	3.0'	10'	10.0'	27	3.5'	2.5'	5'	8.7'	38	3.6'	1.7'
 75W PAR16 NFL (Halogen)		1,900	2,000	4'	119	2.1'	2.1'	3'	1.7'	137	2.2'	1.9'	3'	3.0'	75	3.5'	2.3'	1'	1.7'	238	2.7'	1.1'
				6'	53	3.2'	3.2'	5'	2.9'	49	3.7'	3.1'	4'	4.0'	42	4.6'	3.0'	2'	3.5'	59	5.5'	2.1'
				8'	30	4.3'	4.3'	7'	4.0'	25	5.1'	4.3'	5'	5.0'	27	5.8'	5.8'	3'	5.2'	26	8.2'	3.2'
				10'	19	5.4'	5.4'	9'	5.2'	15	6.6'	5.6'	6'	6.0'	19	6.9'	4.5'	4'	6.9'	15	10.9'	4.3'

