



PL-C Cluster 2-Pin Base

PL-C 26W/827/2P/ALTO 10PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information			
Cap-Base	G24d-3	Lamp Current (Nom)	0.335 A
Life to 50% Failures (Nom)	10,000 hour(s)		
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Luminous Flux	1,800 lm		
Color Designation	Incandescent White	Mechanical and Housing	
Correlated Color Temperature (Nom)	2700 K	Net Weight (Piece)	0.142 lb
Luminous Efficacy (rated) (Nom)	68 lm/W		
Color rendering index (CRI)	82	Approval and Application	
		Mercury (Hg) Content (Nom)	1.4 mg
		Energy Consumption kWh/1000 h	32 kWh
Operating and Electrical		Product Data	
Power Consumption	26.5 W	Order product name	PL-C 26W/827/2P/ALTO 10PK

PL-C Cluster 2-Pin Base

Full product name	PL-C 26W/827/2P/ALTO 10PK
Order code	383216
Material Nr. (12NC)	927906182730
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677109554


Numerator - Packs per outer box	10
EAN/UPC - Case	60046677109556

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 26W/827/2P/ALTO 10PK	1-1/16 inch	1-1/16 inch	5-3/16 inch	5-7/8 inch	6-3/4 inch

Photometric data




Spectral Power Distribution Colour - PL-C 26W/827/2P/ALTO 10PK

Lifetime



Life expectancy diagram - 3 hour cycle



Lumen Maintenance Diagram - PL-C 26W/827/2P/ALTO 10PK

PL-C Cluster 2-Pin Base

Lifetime

Life expectancy diagram - 12 hour cycle

