



PL-C Cluster 4-Pin Base

PL-C 18W/841/4P/ALTO 10PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G24q-2
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	1,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	18.0 W


Lamp Current (Nom)	0.230 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Net Weight (Piece)	0.122 lb
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	PL-C 18W/841/4P/ALTO 10PK

PL-C Cluster 4-Pin Base

Full product name	PL-C 18W/841/4P/ALTO 10PK
Order code	383331
Material Nr. (12NC)	927907284030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677240059


Numerator - Packs per outer box	10
EAN/UPC - Case	60046677240051

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 18W/841/4P/ALTO 10PK	1-1/16 inch	1-1/16 inch	4-5/16 inch	5-1/16 inch	5-5/8 inch

Photometric data




Spectral Power Distribution Colour - PL-C 18W/841/4P/ALTO 10PK

Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

PL-C Cluster 4-Pin Base

Lifetime



Lumen Maintenance Diagram - PL-C 18W/841/4P/ALTO 10PK

