



TL-D LIFEMAX Super 80

36 W G13 Incandescent white Linear fluorescent tube

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15,000 hour(s)
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	827 [CCT of 2700K]
Color Designation	Incandescent White
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	103 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8
Net Weight (Piece)	0.140 kg
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	36 W G13 Incandescent white Linear fluorescent tube
Full product name	36 W G13 Incandescent white Linear fluorescent tube
Full product code	871150028584340
Order code	927982282736
Material Nr. (12NC)	927982282736
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500285843
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500285850



TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
36 W G13 Incandescent white	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
Linear fluorescent tube					

Lifetime



Life expectancy diagram - 3 hour cycle

Life expectancy diagram - 12 hour cycle



Lumen Maintenance Diagram - TL-D 36W/827 1SL/25

