



# MASTER TL Mini Super 80



## MASTER TL Mini Super 80 13W/840 1FM/10X25CC

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G5
Flux measurement reference	Sphere
Life to 50% failures (nom.)	8,000 h

Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	1,000 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	77 lm/W
Colour rendering index (CRI)	82

Operating and Electrical	
Power Consumption	13.1 W
Lamp current (nom.)	0.170 A

Voltage (nom.)	90 V
----------------	------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb shape	T5
Net Weight (Piece)	40.200 g

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	2.5 mg
Mercury (Hg) content (nom.)	3.0 mg
Energy consumption kWh/1,000 hours	14 kWh
EPREL registration number	423503


Product Data	
Order product name	MST TL Mini 13W/840 FAM/10X25BOX

# MASTER TL Mini Super 80

Full product name	MASTER TL Mini Super 80 13W/840 1FM/ 10X25CC
Full EOC	871150071685927
Order code	71685927
Material no. (12 NC)	928001508450
Local order code	1384


Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500716859
Numerator – packs per outer box	250
EAN/UPC – Case	8711500716873

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL Mini 13W/840 FAM/ 10X25BOX	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

## Photometric data



Spectral Power Distribution Colour - MST TL Mini 13W/840 FAM/10X25BOX

