



Preheat T8

F15T8/CW 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	830 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	63
Operating and Electrical	
Power Consumption	15 W
Lamp Current (Nom)	0.335 A
Wattage Equivalent	15 W
Voltage (Nom)	55 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8
Net Weight (Piece)	59.600 g
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	F15T8/CW 25PK
Full product name	F15T8/CW 25PK
Order code	407197
Material Nr. (12NC)	928022803325
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677367206
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677407198


Preheat T8

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/CW 25PK	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data




Spectral Power Distribution Colour - F15T8/CW 25PK

Lifetime



Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

Preheat T8

Lifetime



Lumen Maintenance Diagram - F15T8/CW 25PK

