



TL-D Standard Colours

30 W G13 Cool daylight Linear fluorescent tube

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)		98 V	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Controls and Dimming			
Nominal lifetime	13,000 hour(s)	Dimmable	Yes		
Life to 50% Failures (Nom)	13,000 hour(s)	Mechanical and Housing			
Light Technical		Bulb Shape	T8		
Color Code	54-765	Approval and Application			
Luminous Flux	1,825 lm	Mercury (Hg) Content (Nom)	5.0 mg		
Color Designation	Cool Daylight	Energy Consumption kWh/1000 h	36 kWh		
Correlated Color Temperature (Nom)	6200 K	Product Data			
Color rendering index (CRI)	72	Order product name	30 W G13 Cool daylight Linear fluorescent tube		
Operating and Electrical		Full product name	30 W G13 Cool daylight Linear fluorescent tube		
Power Consumption	30.0 W	Full product code	871150072263800		
Lamp Current (Nom)	0.360 A				

TL-D Standard Colours

Order code	928025405482
Material Nr. (12NC)	928025405482
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.130 kg
EAN/UPC - Product/Case	8711500722638


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500722645

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
30 W G13 Cool daylight Linear fluorescent tube	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

Photometric data




Spectral Power Distribution Colour - TL-D 30W/54-765 1SL/25

Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 30W/54-765 1SL/25

