



MASTER MHN-SA

MASTER MHN-SA 1800W/956 230V XW UNP/1

Compact quartz metal halide lamps with double-pinch

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	X830R
Operating position	P15 [Parallel +/-15D or Horizontal(HOR)]
Life to 50% failures (nom.)	5,000 h
Light Technical	
Colour Code	956 [CCT of 5600K]
Colour designation	Daylight
Chromaticity Coordinate X (Nom)	330
Chromaticity Coordinate Y (Nom)	339
Correlated Colour Temperature (Nom)	5600 K
Luminous efficacy (rated) (nom.)	86 lm/W
Colour rendering index (CRI)	86
Arc Length O (Nom)	25 mm
Operating and Electrical	
Power Consumption	1,800.0 W
Voltage (nom.)	120 V


Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	TD40
Net Weight (Piece)	110.000 g
Approval and Application	
Mercury (Hg) content (nom.)	87 mg
Energy consumption kWh/1,000 hours	1,980 kWh
CE mark	Yes
Product Data	
Order product name	MASTER MHN-SA 1800W/956 230V XW UNP/1
Full product name	MASTER MHN-SA 1800W/956 230V XW UNP/1
Full EOC	871150020106500
Order code	928099205130
Material no. (12 NC)	928099205130

MASTER MHN-SA

Local order code	1800MHNSA956R
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291548294
Numerator – packs per outer box	1


EAN/UPC - Case	8711500201065
----------------	---------------

Dimensional drawing




Product	D (max)	O	X	A	C (max)
MASTER MHN-SA 1800W/956 230V XW UNP/1	41 mm	25 mm	25 mm	318 mm	369 mm

Photometric data




Spectral Power Distribution Colour - MASTER MHN-SA 1800W/956 230V XW UNP/1

Lifetime



MHN SA 1800W 956 Life Expectancy Diagram



Lumen Maintenance Diagram - MASTER MHN-SA 1800W/956 230V XW UNP/1

MASTER MHN-SA

