



Architectural MSD

MSD 1200.1CT/3

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G22
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	92,000 lm
Chromaticity Coordinate X (Nom)	323
Chromaticity Coordinate Y (Nom)	328
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	79 lm/W
Color rendering index (CRI)	73
Arc Length O (Nom)	14.0 mm


Operating and Electrical	
Power Consumption	1,200 W
Lamp Current (Nom)	13.8 A
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Net Weight (Piece)	0.344 lb
Approval and Application	
CE mark	Yes
Product Data	
Order product name	MSD 1200.1CT/3

Architectural MSD

Full product name	MSD 1200.1CT/3
Full product code	872790091135000
Order code	245589
Material Nr. (12NC)	928172005114
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8727900911350
Numerator - Packs per outer box	3
EAN/UPC - Case	8727900911367

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 1200.1CT/3	1-11/16 inch	9/16 inch	3-5/16 inch	3-7/16 inch	3-3/8 inch	7-1/4 inch	2-1/8 inch	2-1/8 inch	2-1/16 inch

Photometric data



Spectral Power Distribution Colour - MSD 1200.1CT/3

