



MSD Platinum (Touring/Stage)

MSD Platinum 11 R 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	-
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Color Code	2
Luminous Flux	12,000 lm
Chromaticity Coordinate X (Nom)	0.300
Chromaticity Coordinate Y (Nom)	0.305


Correlated Color Temperature (Nom)	7800 K
Color rendering index (CRI)	-
Arc Length O (Nom)	1.0 mm
Operating and Electrical	
Power Consumption	250 W
Controls and Dimming	
Dimmable	Yes

MSD Platinum (Touring/Stage)

Mechanical and Housing	
Net Weight (Piece)	0.187 lb
Approval and Application	
CE mark	Yes
Product Data	
Order product name	MSD Platinum 11 R 1CT/8
Full product name	MSD Platinum 11 R 1CT/8


Full product code	871869653976700
Order code	303628
Material Nr. (12NC)	928191705314
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696539767
Numerator - Packs per outer box	8
EAN/UPC - Case	8718696539774

Dimensional drawing



Product	D (max)	T (max)	O	C (max)
MSD Platinum 11 R 1CT/8	2-1/16 inch	7/16 inch	1/16 inch	2-1/8 inch

Photometric data



Spectral Power Distribution Colour – MSD Platinum 11 R 1CT/8

