



Ceramalux ALTO

C400S51/ALTO 12PK

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.


Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	112.5 lm/W
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	20
Operating and Electrical	
Power Consumption	401.5 W
Lamp Current (Nom)	4.6 A
Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED18
Net Weight (Piece)	165.000 g
Approval and Application	
Mercury (Hg) Content (Max)	23.5 mg
Product Data	
Order product name	SON 400W E39 ED58 CL SL/12
Full product name	C400S51/ALTO 12PK
Order code	467373
Material Nr. (12NC)	928601139391
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467371
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467376

Ceramalux ALTO

Dimensional drawing



Product
SON 400W E39 ED58 CL SL/12

