



# Ceramalux Non-ALTO

## C50S68/M 12pk

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	540
Chromaticity Coordinate Y (Nom)	415
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	71 lm/W
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	12
Operating and Electrical	
Power Consumption	50.2 W
Lamp Current (Nom)	1.18 A
Voltage (Nom)	52 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	BD17
Net Weight (Piece)	55.000 g
Approval and Application	
Mercury (Hg) Content (Max)	17.7 mg
Product Data	
Order product name	C50S68/M 12pk
Full product name	C50S68/M 12pk
Order code	928601144990
Material Nr. (12NC)	928601144990
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467302
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467307

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
C50S68/M 12pk	55 mm	138 mm

