



Ceramalux ALTO Non-Cycling

C150S55/ALTO NC HPS 1/12PK

Philips Ceramalux High Pressure Sodium Non-Cycling Lamps are a better value than standard high pressure sodium lamps, with longer life and reduced maintenance cost.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® Non-Cycling
Light Technical	
Chromaticity Coordinate X (Nom)	0.525
Chromaticity Coordinate Y (Nom)	0.417
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	96 lm/W
Luminous Efficacy (rated) (Nom)	106 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	150.6 W
Lamp Current (Nom)	3.2 A
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2
Net Weight (Piece)	132.000 g

Approval and Application


Mercury (Hg) Content (Nom)	2 mg
----------------------------	------

Product Data

Order product name	C150S55/ALTO NC HPS 1/12PK
Full product name	C150S55/ALTO NC HPS 1/12PK
Order code	467332
Material Nr. (12NC)	928601156090
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467333
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467338

Ceramalux ALTO Non-Cycling

Dimensional drawing



Product	D	L	C (max)
C150S55/ALTO NC HPS 1/12PK	2.94 inch	5.000 inch	7.75 inch

