



Pulse Start Metal Halide Standard

MS750/BU/PS 6PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Light Technical	
Luminous Flux	53,300 lm
Color Designation	4000 Kelvin
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.4
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	98 lm/W
Luminous Efficacy (rated) (Nom)	109 lm/W
Color rendering index (CRI)	>65
Operating and Electrical	
Power Consumption	750 W
Wattage Equivalent	750 W

Warm-up time to 60% light	<180 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	BT37
Net Weight (Piece)	1.000 g
Approval and Application	
Mercury (Hg) Content (Max)	125 mg
Product Data	
Order product name	MS750/BU/PS 6PK

Pulse Start Metal Halide Standard

Full product name	MS750/BU/PS 6PK
Order code	135400
Material Nr. (12NC)	928601179101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677135409

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677135404

Dimensional drawing

Product	D (max)	C (max)
MS750/BU/PS 6PK	122 mm	282 mm

