



LED Specialty Lamps

0.5C7/LEDnight light/E12/MilkyND120V 2PF

LEDbulb, Others, E12, 2700 K, 30 lm, 15000 hour(s)

LEDbulb, Others, E12, 2700 K, 30 lm, 15000 hour(s), 60 lm/W

Product data

General Information	
Cap-Base	E12
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	30 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	60 lm/W
Color Consistency	ANSI
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	0.5 W
Lamp Current (Nom)	15 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s


Power Factor (Fraction)	0.2
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	194 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	Others
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.022 lb
Approval and Application	
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 °F to 113 °F
Application Conditions	
can it be used in closed luminaires	No

LED Specialty Lamps

Wireless Technology	Not applicable
Product Data	
Order product name	0.5C7/LEDnight light/E12/MilkyND120V 2PF
Full product name	0.5C7/LEDnight light/E12/MilkyND120V 2PF
Order code	574038
Material Nr. (12NC)	929001224613


Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	046677574031
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677574036

Dimensional drawing




Product	D	C
0.5C7/LEDnight light/E12/MilkyND120V 2PF	15/16 inch	2-1/16 inch


Photometric data



Spectral Power Distribution Colour - 0.5C7/LEDnight light/E12/MilkyND120V 2PF





General uniform lighting - 0.5C7/LEDnight light/E12/MilkyND120V 2PF



Light Distribution Diagram - 0.5C7/LEDnight light/E12/MilkyND120V 2PF

LED Specialty Lamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 0.5C7/LEDnight light/E12/MilkyND120V 2PF

