



精選 LEDspot MR16

5W (50W) GU5.3 cap Warm white Non-dimmable Spot

Essential LEDspots MR16 採用 GU5.3 燈座設計，與大多數現有燈具相容，是專為改裝汰換鹵素聚光燈所設計。Essential LEDspots MR16 可發揮重大節能效益，並大幅降低初始投資成本。

产品数据

一般資訊	
燈座基底	GU5.3
標稱使用壽命	15,000 h
切換週期	50,000
額定壽命 (小時)	15,000 h
照明技術	LED
照明技術	
色碼	827 [CCT of 2700K]
光束角 (Nom)	24 °
光通量	400 lm
光強 (標稱)	1,700 cd
色彩名稱	暖白光 (WW)
光效 (額定) (標準)	80.00 lm/W
相關色彩溫度 (規範)	2700 K
色彩一致性	<6
演色性指數 (CRI)	80
LLMF 標稱壽命結束 (規範)	70 %
運轉與電力	
線路頻率	- Hz
輸入頻率	- Hz
耗電量	5 W


燈具電流 (標稱)	580 mA
相等瓦數	50 W
起始時間 (標稱)	0.5 s
達到 60% 光色的熱穩時間	1 s
功率因數 (比值)	0.5
電壓 (標稱)	12 V
溫度	
T 盒上限 (正常情況)	76 °C
控制與調光	
可調光	否
機械與外罩	
燈泡形狀	MR16
認證與應用	
適合補強燈	是
能源消耗 kWh/1000 h	- kWh
符合歐盟 RoHS 標準	是
產品資料	
下訂產品名稱	5W (50W) GU5.3 cap Warm white Non-dimmable Spot

精選 LEDspot MR16

完整產品名稱	5W (50W) GU5.3 cap Warm white Non-dimmable Spot
完整產品代碼	871869657955800
訂單代碼	929001240108
材質 Nr. (12NC)	929001240108
分子 - 每個包裝的數量	1
淨重 (個)	0.045 kg



EAN/UPC - 產品/案例	8718696579558
分子 - 每一外盒包裝	10
EAN/UPC - 箱	8718696579565

二维绘图




Product	D	C
5W (50W) GU5.3 cap Warm white Non-dimmable Spot	50 mm	46 mm

光度数据



Light Distribution Diagram - Essential LED 5-50W 2700K MR16 24D

Accent Lighting Spots - Essential LED 5-50W 2700K MR16 24D



Spectral Power Distribution Colour - Essential LED 5-50W 2700K MR16 24D

精選 LEDspot MR16

壽命



Life Expectancy Diagram



Lumen Maintenance Diagram - Essential LED 5-50W 2700K MR16 24D

