



CorePro LED PLL



CorePro LED PLL HF 16.5W 840 4P 2G11

CorePro, LED, PL-L, HF, 405 mm, 16.5 W, 36W PL-L, 4000 K, 2100 lm, CRI 83, 30000 h

Philips CorePro LED PLL is the ideal uplamping solution for downlights & luminaires in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

Product data

General Information	
Cap base	2G11
Nominal lifetime	30,000 h
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
Warranty period	3 years
Light Technical	
Colour Code	840 [CCT of 4000K]
Beam angle (nom.)	160 degree(s)
Luminous Flux	2,100 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	127.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	83
LLMF at end of nominal lifetime (nom.)	70 %


Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	39000-71000 Hz
Input frequency	39000-71000 Hz
Power Consumption	16.5 W
Lamp current (max.)	420 mA
Lamp current (min.)	290 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (nom.)	53-77 V
LED alternative to fluorescent lamp power	36W PL-L
Inrush current at mains	-
Max. lamp no. on MCB B type 10A – Mains	-
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-

CorePro LED PLL

Max. lamp no. on MCB B type 16A — Mains	-
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-
Ballast Compatibility	HF
Temperature	
T-Case maximum (nom.)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb material	Glass
Product length	405 mm
Bulb shape	PL-L
Net Weight (Piece)	0.160 kg
Approval and Application	
Energy Efficiency Class	E
Energy-saving product	Yes



Approval marks	RoHS compliance
Energy consumption kWh/1,000 hours	17 kWh
EPREL Registration Number	387353
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	-20°C to 45°C
Product Data	
Order product name	CorePro LED PLL HF 16.5W 840 4P 2G11
Full product name	CorePro LED PLL HF 16.5W 840 4P 2G11
Full EOC	871869673974700
Order code	929001381602
Material no. (12 NC)	929001381602
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696739747
Numerator – packs per outer box	10
EAN/UPC - Case	8718696739754

Dimensional drawing



Product	D1	D	A1	A2	A3
CorePro LED PLL HF 16.5W 840 4P 2G11	17 mm	38 mm	330 mm	405 mm	412 mm

Photometric data




General uniform lighting - CorePro LED PLL HF 16.5W 840 4P 2G11

Spectral Power Distribution Colour - CorePro LED PLL HF 16.5W 840 4P 2G11


CorePro LED PLL

Photometric data




Light Distribution Diagram - CorePro LED PLL HF 16.5W 840 4P 2G11


Lifetime




Lumen Maintenance Diagram - CorePro LED PLL HF 16.5W 840 4P 2G11



LEDtube PLC 400mm 16-5W 2G11 830 2000lm




LEDtube PLC 400mm 16-5W 2G11 830 2000lm



LEDtube PLC 400mm 16-5W 2G11 830 2000lm

CorePro LED PLL

Lifetime



Lumen Maintenance Diagram - CorePro LED PLL HF 16.5W 840 4P 2G11

