



TrueForce High Lumen PAR

23PAR30s/PER/930/F25/ND/120V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	1,900 lm
Luminous Intensity (Nom)	9,000 cd
Luminous Efficacy (rated) (Nom)	82.00 lm/W
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	23 W


Lamp Current (Nom)	206 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	94 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Aluminum
Bulb Shape	PAR30S
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh

TrueForce High Lumen PAR

EU RoHS compliant	Yes
Product Data	
Order product name	23PAR30s/PER/930/F25/ND/120V 6/1FB
Full product name	23PAR30s/PER/930/F25/ND/120V 6/1FB
Order code	929001917504
Material Nr. (12NC)	929001917504



Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.220 kg
EAN/UPC - Product/Case	046677534691
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677534696

Dimensional drawing




Product	D	C
23PAR30s/PER/930/F25/ND/120V 6/1FB	96 mm	94 mm

Photometric data



Accent Lighting Spots - 23PAR30s/PER/930/F25/ND/120V 6/1FB



Spectral Power Distribution Colour - 23PAR30s/PER/930/F25/ND/120V 6/1FB



Light Distribution Diagram - 23PAR30s/PER/930/F25/ND/120V 6/1FB

TrueForce High Lumen PAR

Lifetime



LEDspot PAR30 1FB

Lumen Maintenance Diagram - 23PAR30s/PER/930/F25/ND/120V 6/1FB

