



MASTER LEDtube EM/ Mains



MASTER LEDtube 1200mm HO 12.5W 840 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Warnings and Safety

• -

Product data

General Information	
Cap base	G13 ROT
Nominal lifetime	75,000 h
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
Light Technical	
Colour Code	840 [CCT of 4000K]
Beam angle (nom.)	160 degree(s)
Luminous Flux	2,100 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	168 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	12.5 W
Lamp current (max.)	63 mA
Lamp current (min.)	52 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (nom.)	220-240 V
LED alternative to fluorescent lamp power	36 W
Inrush current at mains	8
Max. lamp no. on MCB B type 10A – Mains	90
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	115

MASTER LEDtube EM/Mains

Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	15
Max. lamp no. on MCB B type 16A – Mains	150
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	190
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	25
Ballast Compatibility	EM/Mains

Temperature

T-Case maximum (nom.)	50 °C
-----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Frosted
Bulb material	Plastic
Product length	1,200 mm
Bulb shape	T8
Net Weight (Piece)	0.230 kg

Approval and Application


Energy Efficiency Class	C
Energy-saving product	Yes

Approval marks	RoHS compliance CE marking KEMA Keur certificate ENEC certificate
Energy consumption kWh/1,000 hours	13 kWh
EPREL Registration Number	1206967
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM)	0.5
Stroboscopic effect	0.2
Ambient temperature range	-20°C to 45°C

Product Data

Order product name	MAS LEDtube 1200mm HO 12.5W 840 T8
Full product name	MASTER LEDtube 1200mm HO 12.5W 840 T8
Full EOC	871869959237000
Order code	59237000
Material no. (12 NC)	929001922702
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699592370
Numerator – packs per outer box	10
EAN/UPC – Case	8718699592387


Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm HO 12.5W 840 T8	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

MASTER LEDtube EM/Mains


Photometric data



General uniform lighting - MAS LEDtube 1200mm HO 12.5W 840 T8




Spectral Power Distribution Colour - MAS LEDtube 1200mm HO 12.5W 840 T8




Light Distribution Diagram - MAS LEDtube 1200mm HO 12.5W 840 T8

Lifetime





Lumen Maintenance Diagram - MAS LEDtube 1200mm HO 12.5W 840 T8



Lumen Maintenance Diagram - MAS LEDtube 1200mm HO 12.5W 840 T8


MASTER LEDtube EM/Mains

Lifetime



LEDtube-75K-5070-FailureRate-LED

Life Expectancy Diagram



LifetimeVsTc

