



# LEDLamps

## LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Product data


<b>General Information</b>		<b>Temperature</b>	
Cap-Base	E27	Lamp Current (Nom)	135 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	120 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	12,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.51
<b>Light Technical</b>		Voltage (Nom)	220-240 V
Color Code	830 [CCT of 3000K]	<b>Controls and Dimming</b>	
Color Code	830 [CCT of 3000K]	Dimmable	No
Beam Angle (Nom)	150 degree(s)	<b>Mechanical and Housing</b>	
Luminous Flux	1,650 lm	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	113 lm/W	Bulb Material	Plastic
Color Designation	White (WH)	Bulb Shape	A67
Correlated Color Temperature (Nom)	3000 K	<b>Approval and Application</b>	
Color Consistency	<6	Energy Consumption kWh/1000 h	15 kWh
Color rendering index (CRI)	80	EyeComfort	No
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Photobiological safety according to EN 62471	RG1		
<b>Operating and Electrical</b>			
Input Frequency	50 to 60 Hz		
Power Consumption	14.5 W		

LEDLamps

EU RoHS compliant	Yes
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR
Full product name	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR



Full product code	871869964047700
Order code	929002003849
Material Nr. (12NC)	929002003849
Net Weight (Piece)	0.131 kg
EAN/UPC - Product/Case	8718699640477
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699640484

Dimensional drawing



Product	D	C
LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	68 mm	132 mm


Photometric data



General uniform lighting - LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR

Light Distribution Diagram - LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR

Photometric data




Spectral Power Distribution Colour - LEDBulb 14.5W E27 3000K 230VA67  
1CT/6APR

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 14.5W E27 3000K 230VA67 1CT/  
6APR

