



MASTER VALUE LEDspot MV

MASTERLEDspot VLE D 6.2-80W GU10 927 36D UK

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap base	GU10
Nominal lifetime	25,000 h
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Colour Code	927 [CCT of 2700K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	575 lm
Luminous intensity (nom.)	850 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	92.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	575 lm
Photobiological safety according to EN 62471	RG1

MASTER VALUE LEDspot MV

Operating and Electrical

Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	6.2 W
Lamp current (nom.)	33 mA
Wattage equivalent	80 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.88
Voltage (nom.)	220-240 V

Temperature

T-Case maximum (nom.)	80 °C
-----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb shape	PAR16
Net Weight (Piece)	0.038 kg

Approval and Application

Energy Efficiency Class	F
Suitable for accent lighting	Yes

Energy consumption kWh/1,000 hours	7 kWh
EPREL Registration Number	391905
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4


Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	MASLEDspot VLE D 6.2-80W GU10 927 36D UK
Full product name	MASTERLEDspot VLE D 6.2-80W GU10 927 36D UK
Full EOC	871869967541701
Order code	67541701
Material no. (12 NC)	929002059599
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699675417
Numerator – packs per outer box	10
EAN/UPC - Case	8719514405677


Dimensional drawing




Product	D	C
MASLEDspot VLE D 6.2-80W GU10 927 36D UK	50 mm	54 mm

MASTER VALUE LEDspot MV


Photometric data



Light Distribution Diagram - MASLEDspot VLE D 6.2-80W GU10 927 36D UK




Spectral Power Distribution Colour - MASLEDspot VLE D 6.2-80W GU10 927 36D UK




Technical Parameters (1) Photo Lighting (3) Page 11

Accent Lighting Spots - MASLEDspot VLE D 6.2-80W GU10 927 36D UK

Lifetime



Lumen Maintenance Diagram - MASLEDspot VLE D 6.2-80W GU10 927 36D UK



25K LED

MASTER VALUE LEDspot MV

