



# CorePro LEDspot MV



## CorePro LEDspot 4-50W GU10 830 36D DIM

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

### Product data

General Information	
Cap-Base	GU10
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	345 lm
Luminous Intensity (Nom)	700 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	345 lm
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	23 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.84
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Shape	PAR16
Net Weight (Piece)	0.048 kg

# CorePro LEDspot MV

## Approval and Application

Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	391911
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4


## Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

## Product Data


Order product name	CorePro LEDspot 4-50W GU10 830 36D DIM
Full product name	CorePro LEDspot 4-50W GU10 830 36D DIM
Full product code	871951435883600
Order code	929002068302
Material Nr. (12NC)	929002068302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514358836
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514358843

## Dimensional drawing




Product	D	C
CorePro LEDspot 4-50W GU10 830 36D DIM	50 mm	54 mm

## Photometric data




Spectral Power Distribution Colour - CorePro LEDspot 4-50W GU10 830 36D DIM



Light Distribution Diagram - CorePro LEDspot 4-50W GU10 830 36D DIM



# CorePro LEDspot MV

## Photometric data



Accent Lighting Spots - CorePro LEDspot 4-50W GU10 830 36D DIM

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - CorePro LEDspot 4-50W GU10 830 36D DIM

