

Corepro InstantFit (UL Type-A) T8

10T8/COR/48-835/IF15/G/DIM 10/1

CorePro, LED, T8, 10 W, 3500 K, 1500 lm, 70000 hour(s)

The CorePro InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only CorePro InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality CorePro InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the CorePro InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	70,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED

Light Technical	
Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	1,500 lm
Color Designation	White (WH)

Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	160.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	25000-105000 Hz
Input Frequency	25000-105000 Hz
Power Consumption	10 W
Lamp Current (Max)	260 mA

Corepro InstantFit (UL Type-A) T8

Lamp Current (Min)	100 mA
Wattage Equivalent	32 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277, 347 V
UL Type	UL Type A

Temperature

T-Case Maximum (Nom)	50 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	T8
Net Weight (Piece)	0.230 kg

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C


Application Conditions

can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data



Order product name	10T8/COR/48-835/IF15/G/DIM 10/1
Full product name	10T8/COR/48-835/IF15/G/DIM 10/1
Order code	553222
Material Nr. (12NC)	929002252834
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677553227
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677553222

Dimensional drawing



Product	D1	D2	A1	A2	A3
10T8/COR/48-835/IF15/G/DIM 10/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm

Photometric data




Accent Lighting Spots - 10T8/COR/48-835/IF15/G/DIM 10/1

Spectral Power Distribution Colour - 10T8/COR/48-835/IF15/G/DIM 10/1


Corepro InstantFit (UL Type-A) T8

Photometric data




Light Distribution Diagram - 10T8/COR/48-835/IF15/G/DIM 10/1


Lifetime




LEDtube 70K 5070 FailureRate-LED



Life Expectancy Diagram




LEDtube 70K 5070 LifetimeVsTc-LED



Lumen Maintenance Diagram - 10T8/COR/48-835/IF15/G/DIM 10/1

Corepro InstantFit (UL Type-A) T8

Lifetime



Lumen Maintenance Diagram - 10T8/COR/48-835/IF15/G/DIM 10/1

