



Trueforce CorePro LED HPL

TForce Core LED HPL 13W E27 840 FR

CorePro, LED HPL, Oval, Mains only, 13 W, HPL 50W, E27, 4000 K, 2000 lm, CRI 80, 25000 h

Philips TrueForce Core LED HPL lamps are an easy, LED solution with a short pay-back to replace High-Intensity Discharge (HID) lamps. This new generation of LED Core post-top lamps brings all the energy-efficiency and long-lifetime benefits of LED-to-HID replacement, while delivering instant saving for a low initial investment. Furthermore, TrueForce CorePro LED HPL lamps are designed to have the same lamp size and light distribution as their HID alternatives. And thanks to our high-power LED filament technology, you'll never know the difference. Plus, their unique IP65 design means that TrueForce Core LED HPL Post-Top lamps can be used for outdoor, as well as indoor applications.

Warnings and Safety

• Installation must always be performed by a qualified electrician or installer. Use the installation guide for instructions.

Product data

General Information		Light Technical	
Cap base	E27	Colour Code	840 [CCT of 4000K]
Nominal lifetime	25,000 h	Beam angle (nom.)	300 degree(s)
Switching Cycle	50,000	Luminous Flux	2,000 lm
Lighting Technology	LED HPL	Colour designation	Cool White (CW)
Flux measurement reference	Sphere	Correlated Colour Temperature (Nom)	4000 K
Warranty period	3 years	Luminous efficacy (rated) (nom.)	153 lm/W
		Colour consistency	<6
		Colour rendering index (CRI)	80

Trueforce CorePro LED HPL

LLMF at end of nominal lifetime (nom.)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical

Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	13 W
Lamp current (nom.)	97 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (nom.)	220-240 V
Inrush current at mains	5.9
Max. lamp no. on MCB B type 10A – Mains	53
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – Mains	85
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-
Wattage Equivalent (LED HID only)	HPL 50W
Ballast Compatibility	Mains only

Temperature

T-Case maximum (nom.)	38.2 °C
-----------------------	---------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Frosted
-------------	---------

Bulb material	Glass
Bulb shape	Oval
Net Weight (Piece)	0.130 kg

Approval and Application

Energy Efficiency Class	D
Energy-saving product	Yes
Energy consumption kWh/1,000 hours	13 kWh
EPREL Registration Number	403619
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM)	1
Stroboscopic effect	1.6
Ambient temperature range	-30 to +45 °C


Application Conditions

Can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data

Order product name	TForce Core LED HPL 13W E27 840 FR
Full product name	TForce Core LED HPL 13W E27 840 FR
Full EOC	871869975027500
Order code	929002349802
Material no. (12 NC)	929002349802
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699750275
Numerator – packs per outer box	6
EAN/UPC - Case	8718699750282



Dimensional drawing



Product	D	C
TForce Core LED HPL 13W E27 840 FR	76 mm	183 mm



Trueforce CorePro LED HPL

Photometric data




Spectral Power Distribution Colour - TForce Core LED HPL 13W E27 840 FR

Light Distribution Diagram - TForce Core LED HPL 13W E27 840 FR



Spectral Power Distribution Colour - TForce Core LED HPL 13W E27 840 FR

Light Distribution Diagram - TForce Core LED HPL 13W E27 840 FR




© 2024 Philips Lighting B.V. All rights reserved. Page 11

General uniform lighting - TForce Core LED HPL 13W E27 840 FR

Trueforce CorePro LED HPL

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - TForce Core LED HPL 13W E27 840 FR

