



# Other LEDtube

## LED 2.2W 300mm S14S WW ND 1CT/4

Philips LEDtube integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

### Product data

General Information	
Cap-Base	S14s
Nominal lifetime	30,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	30,000 hour(s)
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	140 degree(s)
Luminous Flux	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	113.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.1
Stroboscopic effect visibility measure (SVM)	0.1

Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	2.2 W
Lamp Current (Nom)	22 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Inrush current at mains	1.5
Max. lamp no. on MCB B type 10A - Mains	159
Max. lamp no. on MCB B type 10A – EM ballast without Comp. Cap.	220
Max. lamp no. on MCB B type 10A – EM ballast with Comp. Cap.	30
Max. lamp no. on MCB B type 16A - Mains	306
Max. lamp no. on MCB B type 16A – EM ballast without Comp. Cap.	330
Max. lamp no. on MCB B type 16A – EM ballast with Comp. Cap.	49

## Other LEDtube

### Temperature

Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	30 °C

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	300 mm
Bulb Shape	Others

### Approval and Application


Energy Efficiency Class	E
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate

Energy Consumption kWh/1000 h	3 kWh
EPREL Registration Number	387349
EyeComfort	Yes

### Product Data



Order product name	LED 2.2W 300mm S14S WW ND 1CT/4
Full product name	LED 2.2W 300mm S14S WW ND 1CT/4
Full product code	871951426356700
Order code	929002444201
Material Nr. (12NC)	929002444201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514263567
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514263574

## Dimensional drawing



Product	D1	D2	A1	A2	A3
LED 2.2W 300mm S14S WW ND 1CT/4	30 mm	30 mm	266.8 mm		299 mm

## Photometric data




Spectral Power Distribution Colour - LED 2.2W 300mm S14S WW ND 1CT/4

General uniform lighting - LED 2.2W 300mm S14S WW ND 1CT/4

# Other LEDtube

## Photometric data




Light Distribution Diagram - LED 2.2W 300mm S14S WW ND 1CT/4


## Lifetime




Life Expectancy Diagram - LED 2.2W 300mm S14S WW ND 1CT/4



Life Expectancy Diagram - LED 2.2W 300mm S14S WW ND 1CT/4




Life Expectancy Diagram - LED 2.2W 300mm S14S WW ND 1CT/4



Lumen Maintenance Diagram - LED 2.2W 300mm S14S WW ND 1CT/4

## Other LEDtube

### Lifetime



Lumen Maintenance Diagram - LED 2.2W 300mm S14S WW ND 1CT/4

