



MASTER VALUE LEDs pot LV



MASTER LED spot VLE D 5.8-35W MR16 930 36D

Philips MASTER VALUE MR16 is the series of Low Voltage (12 VAC) Halogen MR16 replacements. Not only does it employ Philips' patented solution to guarantee the broadest possible compatibility with standard 12 V Halogen electronic transformers, it also delivers beam intensity which is equivalent to the 50 W Philips Halogen MR16 lamps. The form-factor of Philips MASTER Value LED MR16 guarantees a 100% form on the back-side of the lamp (exact fit with Halogen lamps.)

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information		Correlated Colour Temperature (Nom)	
Cap base	GU5.3	Luminous efficacy (rated) (nom.)	3000 K
Nominal lifetime	25,000 h	Colour consistency	79 lm/W
Switching Cycle	50,000	Colour rendering index (CRI)	<6
Lighting Technology	LED	LLMF at end of nominal lifetime (nom.)	90
Flux measurement reference	Narrow Cone	Luminous flux in 90° cone (rated)	70 %
Light Technical		Photobiological safety according to EN 62471	RG1
Colour Code	930 [CCT of 3000K]	Operating and Electrical	
Beam angle (nom.)	36 degree(s)	Line Frequency	- Hz
Luminous Flux	460 lm	Input frequency	- Hz
Luminous intensity (nom.)	1,300 cd	Power Consumption	5.8 W
Colour designation	White (WH)	Lamp current (nom.)	510 mA

MASTER VALUE LEDspot LV

Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	ac electronic 12 V

Temperature

T-Case maximum (nom.)	85 °C
-----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb shape	MR16
Net Weight (Piece)	0.045 kg

Approval and Application

Energy Efficiency Class	F
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	6 kWh
EPREL Registration Number	453174

CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes


Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data


Order product name	MAS LED spot VLE D 5.8-35W MR16 930 36D
Full product name	MASTER LED spot VLE D 5.8-35W MR16 930 36D
Full EOC	871951430720900
Order code	30720900
Material no. (12 NC)	929002492602
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514307209
Numerator – packs per outer box	10
EAN/UPC – Case	8719514307216

Dimensional drawing




Product	D	C
MAS LED spot VLE D 5.8-35W MR16 930 36D	50.5 mm	45.5 mm

Photometric data




Light Distribution Diagram – MAS LED spot VLE D 5.8-35W MR16 930 36D



Spectral Power Distribution Colour – MAS LED spot VLE D 5.8-35W MR16 930 36D

MASTER VALUE LEDspot LV



Photometric data



© 2023 Philips Lighting B.V. All rights reserved. Philips Lighting B.V. is a registered trademark of Koninklijke Philips N.V.

Accent Lighting Spots - MAS LED spot VLE D 5.8-35W MR16 930 36D

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - MAS LED spot VLE D 5.8-35W MR16 930 36D

