



MASTER VALUE LEDs pot LV



MASTER LED SPOT VLE D 7.5-50W MR16 930 36D

Philips MASTER VALUE MR16 is the series of Low Voltage (12 VAC) Halogen MR16 replacements. Not only does it employ Philips' patented solution to guarantee the broadest possible compatibility with standard 12 V Halogen electronic transformers, it also delivers beam intensity which is equivalent to the 50 W Philips Halogen MR16 lamps. The form-factor of Philips MASTER Value LED MR16 guarantees a 100% form on the back-side of the lamp (exact fit with Halogen lamps.)

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap base	GU5.3
Nominal lifetime	25,000 h
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
Light Technical	
Colour Code	930 [CCT of 3000K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	630 lm
Luminous intensity (nom.)	1,600 cd
Colour designation	White (WH)

Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	84 lm/W
Colour consistency	<6
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	630 lm
Photobiological safety according to EN 62471 RG1	
Operating and Electrical	
Line Frequency	- Hz
Input frequency	- Hz
Power Consumption	7.5 W
Lamp current (nom.)	660 mA

MASTER VALUE LEDspot LV

Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	ac electronic 12 V

Temperature

T-Case maximum (nom.)	95 °C
-----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb shape	MR16
Net Weight (Piece)	0.045 kg

Approval and Application

Energy Efficiency Class	F
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	8 kWh
EPREL Registration Number	453181

CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes


Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data



Order product name	MAS LED SPOT VLE D 7.5-50W MR16 930 36D
Full product name	MASTER LED SPOT VLE D 7.5-50W MR16 930 36D
Full EOC	871951430734600
Order code	30734600
Material no. (12 NC)	929002493302
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514307346
Numerator – packs per outer box	10
EAN/UPC – Case	8719514307353

Dimensional drawing



Product	D	C
MAS LED SPOT VLE D 7.5-50W MR16 930 36D	50.5 mm	45.5 mm

Photometric data




Accent Lighting Spots - MAS LED SPOT VLE D 7.5-50W MR16 930 36D

Light Distribution Diagram - MAS LED SPOT VLE D 7.5-50W MR16 930 36D


MASTER VALUE LEDspot LV

Photometric data




Spectral Power Distribution Colour - MAS LED SPOT VLE D 7.5-50W MR16 930 36D

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LED SPOT VLE D 7.5-50W MR16 930 36D

