



LED A15

3.5A15/VIN/820/E26/Amber/G/SP D 4/1PFT20

LEDbulb, A15, 25 W, E26, 2000 K, 225 lm, 15000 hour(s), Glass

LEDbulb, A15, 25 W, E26, 2000 K, 225 lm, 15000 hour(s), Glass, 64 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	820 [CCT of 2000K]
Beam Angle (Nom)	330 degree(s)
Luminous Flux	225 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	64 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	3.5 W
Lamp Current (Nom)	41 mA
Wattage Equivalent	25 W


Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
UL Type	Yes
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Amber
Bulb Material	Glass
Bulb Shape	A15
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.086 lb
Approval and Application	
EU RoHS compliant	Yes
T20 compliant	N/A
Ambient temperature range	-4 °F to 113 °F
Application Conditions	
can it be used in closed luminaires	No

LED A15

Wireless Technology	Not applicable
Product Data	
Order product name	3.5A15/VIN/820/E26/Amber/G/SP D 4/1PFT20
Full product name	3.5A15/VIN/820/E26/Amber/G/SP D 4/1PFT20
Order code	565655
Material Nr. (12NC)	929002987203



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677565657
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677565652

Dimensional drawing



Product	D	C
3.5A15/VIN/820/E26/Amber/G/SP D 4/1PFT20	1-7/8 inch	3-1/4 inch

Photometric data



LED A15

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 3.5A15/VIN/820/E26/Amber/G/SP D
4/1PFT20

