



MASTER LED spot ExpertColor AR111



MAS ExpertColor 14.8-75W 940 AR111 24D

MASTER, LEDspot, AR111, 75 W, G53, 4000 K, 950 lm, CRI 95, 40000 h

The MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot LV and LEDspot Par lamps.

Product data

General Information			
Cap base	G53	Correlated Colour Temperature (Nom)	4000 K
Nominal lifetime	40,000 h	Luminous efficacy (rated) (nom.)	64.00 lm/W
Switching Cycle	50,000	Colour consistency	<4
Lighting Technology	LEDspot	Colour rendering index (CRI)	95
Flux measurement reference	Narrow Cone	LLMF at end of nominal lifetime (nom.)	70 %
Warranty period	5 years	Luminous flux in 90° cone (rated)	950 lm
		Photobiological safety according to EN 62471	RG1
Light Technical		Operating and Electrical	
Colour Code	940 [CCT of 4000K]	Line Frequency	50 to 60 Hz
Beam angle (nom.)	24 degree(s)	Input frequency	50 to 60 Hz
Luminous Flux	950 lm	Power Consumption	14.8 W
Luminous intensity (nom.)	3,300 cd	Lamp current (nom.)	1,500 mA
Colour designation	Cool White (CW)	Wattage equivalent	75 W

MASTER LED spot ExpertColor AR111

Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	ac electronic 12 V

Temperature

T-Case maximum (nom.)	85 °C
-----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	AR111
Net Weight (Piece)	0.160 kg

Approval and Application

Energy Efficiency Class	G
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	15 kWh
EPREL Registration Number	648253
CE mark	Yes

EU RoHS compliant	Yes
EyeComfort	Yes
Ambient temperature range	-20 to +45 °C


Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	MAS ExpertColor 14.8-75W 940 AR111 24D
Full product name	MAS ExpertColor 14.8-75W 940 AR111 24D
Full EOC	871951433387100
Order code	929003043002
Material no. (12 NC)	929003043002
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514333871
Numerator – packs per outer box	6
EAN/UPC - Case	8719514333888


Dimensional drawing




Product	D	C
MAS ExpertColor 14.8-75W 940 AR111 24D	111 mm	61 mm

MASTER LED spot ExpertColor AR111


Photometric data



Light Distribution Diagram - MAS ExpertColor 14.8-75W 940 AR111 24D




Spectral Power Distribution Colour - MAS ExpertColor 14.8-75W 940 AR111 24D




© 2023 Philips Lighting B.V. All rights reserved. Page 11

Accent Lighting Spots - MAS ExpertColor 14.8-75W 940 AR111 24D

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS ExpertColor 14.8-75W 940 AR111 24D

MASTER LED spot ExpertColor AR111

