

MASTER LED tube Mains T5



MAS LEDtube 1200mm HE 16.5W 830 T5 EU

MASTER, LEDtube, T5, Mains, 1200 mm, 16.5 W, 28W TL5 HE, 3000 K, 2300 lm, CRI 80, 60000 h

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! . Perfectly safe, reliable & easy to install, the Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximise value over lifetime with high energy savings and lower maintenance costs.

Product data

General Information		Luminous efficacy (rated) (nom.)		139 lm/W
Cap base	G5	Colour consistency	<6	
Nominal lifetime	60,000 h	Colour rendering index (CRI)	80	
Switching Cycle	200,000	LLMF at end of nominal lifetime (nom.)	70 %	
Lighting Technology	LEDtube	Photobiological safety according to EN 62471	RG0	
Flux measurement reference	Sphere			
Warranty period	5 years			
Light Technical		Operating and Electrical		
Colour Code	830 [CCT of 3000K]	Line Frequency	50 to 60 Hz	
Beam angle (nom.)	200 degree(s)	Input frequency	50 to 60 Hz	
Luminous Flux	2,300 lm	Power Consumption	16.5 W	
Colour designation	White (WH)	Lamp current (nom.)	85 mA	
Correlated Colour Temperature (Nom)	3000 K	Starting time (nom.)	0.5 s	
		Warm-up time to 60% light	0.5 s	
		Power Factor (Fraction)	0.9	

MASTER LED tube Mains T5

Voltage (nom.)	220-240 V
LED alternative to fluorescent lamp power	28W TL5 HE
Inrush current at mains	7
Max. lamp no. on MCB B type 10A – Mains	76
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – Mains	121
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-
Ballast Compatibility	Mains

Temperature

T-Case maximum (nom.)	55 °C
-----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Frosted
Bulb material	Glass
Product length	1,200 mm
Bulb shape	T5
Net Weight (Piece)	0.215 kg


Approval and Application

Energy Efficiency Class	D
Energy-saving product	Yes
Approval marks	RoHS compliance CE marking KEMA Keur certificate
Energy consumption kWh/1,000 hours	17 kWh
EPREL Registration Number	1476410
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	MAS LEDtube 1200mm HE 16.5W 830 T5 EU
Full product name	MAS LEDtube 1200mm HE 16.5W 830 T5 EU
Full EOC	871951433431100
Order code	929003044402
Material no. (12 NC)	929003044402
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514334311
Numerator – packs per outer box	10
EAN/UPC – Case	8719514334328



Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm HE 16.5W 830 T5 EU	15.7 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm


MASTER LED tube Mains T5

Photometric data




Light Distribution Diagram - MAS LEDtube 1200mm HE 16.5W 830 T5 EU

General uniform lighting - MAS LEDtube 1200mm HE 16.5W 830 T5 EU




Spectral Power Distribution Colour - MAS LEDtube 1200mm HE 16.5W 830 T5 EU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDtube 1200mm HE 16.5W 830 T5 EU

MASTER LED tube Mains T5

Lifetime



FailureRate

Lumen Maintenance Diagram - MAS LEDtube 1200mm HE 16.5W 830 T5 EU



LifetimeVsTc

