



MASTER LED spot LV

7MR16/LED/830/F25/DIM 12V 10/1FB

LEDspot, MR16, 50 W, GU5.3, 3000 K, 515 lm, 25000 hour(s), Aluminum

LEDspot, MR16, 50 W, GU5.3, 3000 K, 515 lm, 25000 hour(s), Aluminum, 73.00 lm/W

Product data

General Information	
Cap-Base	GU5.3
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	515 lm
Luminous Intensity (Nom)	2,500 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	73.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	7 W


Lamp Current (Nom)	650 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	194 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Aluminum
Bulb Shape	MR16
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.132 lb
Approval and Application	
Suitable For Accent Lighting	Yes

MASTER LED spot LV

EU RoHS compliant	Yes
T20 compliant	No
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Product Data	
Order product name	7MR16/LED/830/F25/DIM 12V 10/1FB


Full product name	7MR16/LED/830/F25/DIM 12V 10/1FB
Order code	573873
Material Nr. (12NC)	929003076304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677573874
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677573879

Dimensional drawing




Product	D	C
7MR16/LED/830/F25/DIM 12V 10/1FB	2 inch	1-7/8 inch

Photometric data




Spectral Power Distribution Colour - 7MR16/LED/830/F25/DIM 12V 10/1FB



Light Distribution Diagram - 7MR16/LED/830/F25/DIM 12V 10/1FB

MASTER LED spot LV



Photometric data



Technical Information 1.1 Philips Lighting B.V. Page 10

Accent Lighting Spots - 7MR16/LED/830/F25/DIM 12V 10/1FB

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 7MR16/LED/830/F25/DIM 12V 10/1FB

