



MASTER LED spot ExpertColor LV



MASTER LED ExpertColor 7.5–43W MR16 930 36D

MASTER, LED, MR16, Only with specific dimmers, GU5.3, 3000 K, 500 lm, CRI 92, 40000 h

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV lamps.


Product data

General Information			
Cap base	GU5.3	Correlated Colour Temperature (Nom)	3000 K
Nominal lifetime	40,000 h	Luminous efficacy (rated) (nom.)	66 lm/W
Switching Cycle	50,000	Colour consistency	<3
Lighting Technology	LED	Colour rendering index (CRI)	92
Flux measurement reference	Narrow Cone	LLMF at end of nominal lifetime (nom.)	70 %
Warranty period	5 years	Luminous flux in 90° cone (rated)	500 lm
		Photobiological safety according to EN 62471	RG1
Light Technical		Operating and Electrical	
Colour Code	930 [CCT of 3000K]	Line Frequency	- Hz
Beam angle (nom.)	36 degree(s)	Input frequency	- Hz
Luminous Flux	500 lm	Power Consumption	7.5 W
Luminous intensity (nom.)	1,550 cd	Lamp current (nom.)	720 mA
Colour designation	White (WH)	Wattage equivalent	43 W


MASTER LED spot ExpertColor LV

Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	ac electronic 12 V
Temperature	
T-Case maximum (nom.)	93 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb shape	MR16
Net Weight (Piece)	0.052 kg
Approval and Application	
Energy Efficiency Class	G
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	8 kWh
EPREL Registration Number	624224
CE mark	Yes

Dimensional drawing




Photometric data



Accent Lighting Spots - MAS LED ExpertColor 7.5-43W MR16 930 36D

EU RoHS compliant	Yes
EyeComfort	Yes
Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	MAS LED ExpertColor 7.5-43W MR16 930 36D
Full product name	MASTER LED ExpertColor 7.5-43W MR16 930 36D
Full EOC	871951435873700
Order code	35873700
Material no. (12 NC)	929003080102
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514358737
Numerator – packs per outer box	10
EAN/UPC - Case	8719514358744


Product	D	C
MAS LED ExpertColor 7.5-43W MR16 930 36D	50.5 mm	46 mm



Spectral Power Distribution Colour - MAS LED ExpertColor 7.5-43W MR16 930 36D


MASTER LED spot ExpertColor LV

Photometric data




Light Distribution Diagram - MAS LED ExpertColor 7.5-43W MR16 930 36D

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LED ExpertColor 7.5-43W MR16 930 36D

