



MASTER LED spot ExpertColor LV

6.3MR16/LED/F25/927/D/EC/12V T20 10/1FB

LEDspot, MR16, 42 W, GU5.3, 2700 K, 470 lm, 25000 hour(s), Aluminum

LEDspot, MR16, 42 W, GU5.3, 2700 K, 470 lm, 25000 hour(s), Aluminum, 74.00 lm/W

Product data

General Information	
Cap-Base	GU5.3
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	470 lm
Luminous Intensity (Nom)	1,960 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	74.00 lm/W
Color Consistency	<3
Color rendering index (CRI)	91
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	- Hz


Input Frequency	- Hz
Power Consumption	6.3 W
Lamp Current (Nom)	600 mA
Wattage Equivalent	42 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	192 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Aluminum
Bulb Shape	MR16
UL Wet/ damp/ dry location	Damp location

MASTER LED spot ExpertColor LV

Net Weight (Piece)	0.115 lb
Approval and Application	
Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Product Data	
Order product name	6.3MR16/LED/F25/927/D/EC/12V T20 10/1FB
Full product name	6.3MR16/LED/F25/927/D/EC/12V T20 10/1FB
Order code	573535
Material Nr. (12NC)	929003080304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677573539
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677573534

Dimensional drawing




Product	D	C
6.3MR16/LED/F25/927/D/EC/12V T20 10/1FB	2 inch	1-13/16 inch

Photometric data




Light Distribution Diagram - 6.3MR16/LED/F25/927/D/EC/12V T20 10/1FB



Spectral Power Distribution Colour - 6.3MR16/LED/F25/927/D/EC/12V T20 10/1FB

MASTER LED spot ExpertColor LV



Photometric data



© 2023 Philips Lighting B.V. All rights reserved. Philips Lighting B.V. is a registered trademark of Koninklijke Philips N.V.

Accent Lighting Spots - 6.3MR16/LED/F25/927/D/EC/12V T20 10/1FB

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 6.3MR16/LED/F25/927/D/EC/12V T20 10/1FB

