



LED G16.5

3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20

Philips G16.5 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	350 lm
Color Designation	Warm Glow(WG)
Luminous Efficacy (rated) (Nom)	100 lm/W
Correlated Color Temperature (Nom)	2200 2700 K
Color Consistency	<4
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	3.5 W
Lamp Current (Nom)	40 mA

Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.4 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
Ambient temperature range	-4 °F to 104 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	G16.5
UL Wet/ damp/ dry location	Wet location
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort

LED G16.5

Application Conditions


can it be used in closed luminaires No

Product Data

Order product name	3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20
Full product name	3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20
Order code	573303
Material Nr. (12NC)	929003085203



Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.035 lb
EAN/UPC - Product/Case	046677573300
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677573305

Dimensional drawing




Product	D	C
3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20	2 inch	3-3/16 inch

Photometric data



Light Distribution Diagram - 3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20

Spectral Power Distribution Colour - 3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20



General uniform lighting - 3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20

LED G16.5

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20

