



# Magnetic Sys

## Mag Ad L Spotlight 12.5W 1130lm 40K 24D

Magnetic Sys, 12.5 W, 1130 lm, 4000 K, Beam angle 24°, Black

Magnetic Sys offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance. Also an ideal solution for easy installation and DIY design friendly.

### Product data

General Information	
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	No
Switching Cycle	12,500
Lighting Technology	LED
Warranty period	1 years

Light Technical	
Luminous Flux	1,130 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color rendering index (CRI)	90
Light source color	940 neutral white
Optic type	Beam angle 24°
Luminaire light beam spread	24°

Operating and Electrical	
Input Voltage	48 V
Line Frequency	- Hz
Input Frequency	- Hz

Power Consumption	12.5 W
Power Factor (Fraction)	-
Connection	Connection unit 2-pole
Suitable for random switching	No
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Metal-Plastic
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Polyamide
Housing Color	Black
Optical cover finish	Textured
Overall length	343 mm
Overall width	22 mm

Magnetic Sys

Overall height	100 mm
Dimensions (Height x Width x Depth)	100 x 22 x 343 mm
Net weight	0.395 kg
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.395 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Warranty	3 year(s)
EyeComfort	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	( ( , 0.3818, 0.3833 ) ) <5

Power consumption tolerance	+/-10%
-----------------------------	--------


Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1.5 %
Median useful life L70B50	25,000 hour(s)


Product Data

Order product name	Mag Ad L Spotlight 12.5W 1130lm 40K 24D
Full product name	Mag Ad L Spotlight 12.5W 1130lm 40K 24D
Full product code	692234195489400
Order code	929003207910
Material Nr. (12NC)	929003207910
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341954894
Numerator - Packs per outer box	10
EAN/UPC - Case	6922341954900


Dimensional drawing



Photometric data



Light Distribution Diagram - Mag Ad L Spotlight 12.5W 1130lm 40K 24D



General uniform lighting - Mag Ad L Spotlight 12.5W 1130lm 40K 24D

