



# TrueForce LED Public (Road – SON)

## MAS LED SON-T EM 5.4Klm 34W 727 E27

MASTER, LED SON-T, Tubular, EM/Mains, 34 W, SON-T 70W, E27, 2700 K, 5400 lm, CRI 70, 70000 h

Philips MASTER – LED HID SON-T lamps are an easy LED solution with a short payback period to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. MASTER – LED HID SON-T solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit MASTER – LED HID SON-T lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast (for IF replacements) or reflector.

### Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

### Product data

General Information		Operating and Electrical	
Cap base	E27	Colour designation	Warm White (WW)
Nominal lifetime	70,000 h	Correlated Colour Temperature (Nom)	2700 K
Switching Cycle	50,000	Luminous efficacy (rated) (nom.)	158 lm/W
Lighting Technology	LED SON-T	Colour consistency	<6
Flux measurement reference	Sphere	Colour rendering index (CRI)	70
		LLMF at end of nominal lifetime (nom.)	70 %
		Photobiological safety according to EN 62471	RG1
Light Technical			
Colour Code	727 [CCT of 2700K]	Line Frequency	50 to 60 Hz
Luminous Flux	5,400 lm		

## TrueForce LED Public (Road – SON)

Input frequency	50 to 60 Hz
Power Consumption	34 W
Lamp current (max.)	325 mA
Lamp current (min.)	165 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (nom.)	120–240 V
Inrush current at mains	5.9
Max. lamp no. on MCB B type 10A — Mains	39
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	39
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	7
Max. lamp no. on MCB B type 16A — Mains	62
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	62
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	11
Wattage Equivalent (LED HID only)	SON-T 70W
Ballast Compatibility	EM/Mains

### Temperature

T-Case maximum (nom.)	59 °C
-----------------------	-------

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Lamp Finish	Clear
-------------	-------

Bulb material	Glass
Bulb shape	Tubular
Net Weight (Piece)	0.285 kg


### Approval and Application

Energy Efficiency Class	D
Energy-saving product	Yes
Energy consumption kWh/1,000 hours	34 kWh
EPREL Registration Number	1077803
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM)	1
Stroboscopic effect	2.5
Ambient temperature range	-30 to +45 °C

### Product Data

Order product name	MAS LED SON-T EM 5.4Klm 34W 727 E27
Full product name	MAS LED SON-T EM 5.4Klm 34W 727 E27
Full EOC	871951444909100
Order code	929003468118
Material no. (12 NC)	929003468118
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514449091
Numerator – packs per outer box	6
EAN/UPC – Case	8719514449107


## Dimensional drawing




Product	D	C
MAS LED SON-T EM 5.4Klm 34W 727 E27	61 mm	200 mm

# TrueForce LED Public (Road – SON)


## Photometric data



Spectral Power Distribution Colour - MAS LED SON-T EM 5.4Klm 34W 727 E27




Light Distribution Diagram - MAS LED SON-T EM 5.4Klm 34W 727 E27




General uniform lighting - MAS LED SON-T EM 5.4Klm 34W 727 E27

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LED SON-T EM 5.4Klm 34W 727 E27

## TrueForce LED Public (Road – SON)

