



# MASTER VALUE LED spot PAR



## MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D

MASTER Value, LEDspot, PAR30S, 75 W, E27, 2700 K, 740 lm, CRI 90, 25000 h, Glass

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. It's a dimmable solution. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. The product offers more energy saving comparing with normal LED spots.

### Product data


General Information		Colour consistency	
Cap base	E27	Colour consistency	<6
Nominal lifetime	25,000 h	Colour rendering index (CRI)	90
Switching Cycle	50,000	LLMF at end of nominal lifetime (nom.)	70 %
Lighting Technology	LEDspot	Luminous flux in 90° cone (rated)	740 lm
Flux measurement reference	Narrow Cone	Photobiological safety according to EN 62471	RG1
Warranty period	5 years		
Light Technical		Operating and Electrical	
Colour Code	927 [CCT of 2700K]	Line Frequency	50 to 60 Hz
Beam angle (nom.)	25 degree(s)	Input frequency	50 to 60 Hz
Luminous Flux	740 lm	Power Consumption	9.5 W
Luminous intensity (nom.)	3,000 cd	Lamp current (nom.)	60 mA
Colour designation	Warm White (WW)	Wattage equivalent	75 W
Correlated Colour Temperature (Nom)	2700 K	Starting time (nom.)	0.5 s
Luminous efficacy (rated) (nom.)	77 lm/W	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7

# MASTER VALUE LED spot PAR

Voltage (nom.)	220-240 V
<b>Temperature</b>	
T-Case maximum (nom.)	80 °C
<b>Controls and Dimming</b>	
Dimmable	Only with specific dimmers
<b>Mechanical and Housing</b>	
Lamp Finish	Clear
Bulb material	Glass
Bulb shape	PAR30S
Net Weight (Piece)	0.160 kg
<b>Approval and Application</b>	
Energy Efficiency Class	F
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	10 kWh
EPREL Registration Number	1121746
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes

Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20 to +45 °C
<b>Application Conditions</b>	
Can it be used in closed luminaires	No
<b>Product Data</b>	
Order product name	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D
Full product name	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D
Full EOC	871951444320400
Order code	929003485402
Material no. (12 NC)	929003485402
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514443204
Numerator – packs per outer box	6
EAN/UPC - Case	8719514443211



## Dimensional drawing



Product	D	C
MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	95 mm	86 mm


# MASTER VALUE LED spot PAR

## Photometric data




Accent Lighting Spots - MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D

Spectral Power Distribution Colour - MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D




Light Distribution Diagram - MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D

## MASTER VALUE LED spot PAR

