

CorePro LED tube EM/ Mains T8

CorePro LEDtube 1200mm 15.5W 830 T8

CorePro, LEDtube, T8, EM/Mains, 47-1/4 inch, 15.5 W, 36W TL-D, 3000 K, 1700 lm, CRI 80, 50000 hour(s)

CorePro, LEDtube, T8, EM/Mains, 47-1/4 inch, 15.5 W, LED alternative to 36W TL-D, 3000 K, 1700 lm, CRI 80, 50000 hour(s), 109 lm/W, EEL F, G13, Beam angle 240 degree(s), Glass, 1200 mm, RG0, SDCM 6, PF 0.9, IP20, SVM 0.4, PstLM 1

Warnings and Safety

• -

Product data

General Information	
Cap-Base	G13
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LEDtube
Flux measurement reference	Sphere
Warranty period	3 years
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	1,700 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	109 lm/W

Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	15.5 W
Lamp Current (Nom)	84 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	36W TL-D

CorePro LED tube EM/Mains T8

Inrush current at mains	5.08
Max. lamp no. on MCB B type 10A – Mains	91
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	91
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	24
Max. lamp no. on MCB B type 16A – Mains	145
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	145
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	38
Ballast Compatibility	EM/Mains

Temperature

T-Case Maximum (Nom)	140 °F
----------------------	--------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	47-1/4 inch
Bulb Shape	T8
Net Weight (Piece)	0.485 lb

Approval and Application

Energy Efficiency Class	F
Energy Saving Product	Yes

Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
EPREL Registration Number	1827706
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM) – Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-4 to +113 °F


Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data

Order product name	CorePro LEDtube 1200mm 15.5W 830 T8
Full product name	CorePro LEDtube 1200mm 15.5W 830 T8
Full product code	871951448640900
Order code	929003577232
Material Nr. (12NC)	929003577232
Numerator – Quantity Per Pack	1
EAN/UPC – Product/Case	8719514486409
Numerator – Packs per outer box	20
EAN/UPC – Case	8719514486416

Dimensional drawing




D1	D2	A1	A2	A3
25.7mm	28mm	1198mm	1205mm	1212mm


Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 15.5W 830 T8	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

CorePro LED tube EM/Mains T8


Photometric data



Spectral Power Distribution Colour - CorePro LEDtube 1200mm 15.5W 830 T8




Light Distribution Diagram - CorePro LEDtube 1200mm 15.5W 830 T8




General uniform lighting - CorePro LEDtube 1200mm 15.5W 830 T8

Lifetime



Lumen Maintenance Diagram - CorePro LEDtube 1200mm 15.5W 830 T8



Life Expectancy Diagram

CorePro LED tube EM/Mains T8

Lifetime



LifetimeVsTc



FailureRate

Lumen Maintenance Diagram - CorePro LEDtube 1200mm 15.5W 830 T8

