



CorePro LED PLL



CorePro LED PLL EM/Mains 16.5W 840 4P

CorePro, LED, PL-L, EM, 405 mm, 16.5 W, 36W PL-L, 4000 K, 2100 lm, CRI 80, 30000 h

Philips CorePro LED PLL is the ideal uplamping solution for downlights & luminaires in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

Product data

General Information	
Cap base	2G11
Nominal lifetime	30,000 h
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
Warranty period	3 years
Light Technical	
Colour Code	840 [CCT of 4000K]
Beam angle (nom.)	160 degree(s)
Luminous Flux	2,100 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	127 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Photobiological safety according to EN 62471	RGO
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	16.5 W
Lamp current (nom.)	83 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (nom.)	220-240 V
LED alternative to fluorescent lamp power	36W PL-L
Inrush current at mains	9.4
Max. lamp no. on MCB B type 10A — Mains	82
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	104
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	19
Max. lamp no. on MCB B type 16A — Mains	131

CorePro LED PLL


Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	166
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	30
Ballast Compatibility	EM
Temperature	
T-Case maximum (nom.)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb material	Glass
Product length	405 mm
Bulb shape	PL-L
Net Weight (Piece)	0.150 kg
Approval and Application	
Energy Efficiency Class	E
Energy-saving product	Yes
Approval marks	RoHS compliance KEMA Keur certificate

Energy consumption kWh/1,000 hours	17 kWh
EPREL Registration Number	1370828
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20°C to 45°C

Product Data

Order product name	CorePro LED PLL EM/Mains 16.5W 840 4P
Full product name	CorePro LED PLL EM/Mains 16.5W 840 4P
Full EOC	872016915709500
Order code	929003592702
Material no. (12 NC)	929003592702
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169157095
Numerator – packs per outer box	10
EAN/UPC - Case	8720169157101



Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLL EM/Mains 16.5W 840 4P	17 mm	38 mm	330 mm	405 mm	412 mm


CorePro LED PLL

Photometric data




General uniform lighting - CorePro LED PLL EM/Mains 16.5W 840 4P

Spectral Power Distribution Colour - CorePro LED PLL EM/Mains 16.5W 840 4P




Light Distribution Diagram - CorePro LED PLL EM/Mains 16.5W 840 4P

Lifetime





Lumen Maintenance Diagram - CorePro LED PLL EM/Mains 16.5W 840 4P




FailureRate

CorePro LED PLL

Lifetime



Life Expectancy Diagram



LifetimeVsTc

Lumen Maintenance Diagram - CorePro LED PLL EM/Mains 16.5W 840 4P

