



CorePro LED PLL



CorePro LED PLL Mains 24W 830 4P

CorePro, LED, PL-L, Mains, 528 mm, 24 W, 55W PL-L, 3000 K, 3200 lm, CRI 80, 30000 h

Philips CorePro LED PLL is the ideal uplamping solution for downlights & luminaires in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

Product data

General Information	
Cap base	2G11
Nominal lifetime	30,000 h
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
Warranty period	3 years
Light Technical	
Colour Code	830 [CCT of 3000K]
Beam angle (nom.)	160 degree(s)
Luminous Flux	3,200 lm
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	133 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	24 W
Lamp current (nom.)	127 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (nom.)	220-240 V
LED alternative to fluorescent lamp power	55W PL-L
Inrush current at mains	9.6
Max. lamp no. on MCB B type 10A — Mains	80
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	80
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	16
Max. lamp no. on MCB B type 16A — Mains	128

CorePro LED PLL

Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	128
--	-----

Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	25
---	----

Ballast Compatibility	Mains
-----------------------	-------

Temperature

T-Case maximum (nom.)	75 °C
-----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Frosted
-------------	---------

Bulb material	Glass
---------------	-------

Product length	528 mm
----------------	--------

Bulb shape	PL-L
------------	------

Net Weight (Piece)	0.192 kg
--------------------	----------

Approval and Application

Energy Efficiency Class	E
-------------------------	---

Energy-saving product	Yes
-----------------------	-----

Approval marks	RoHS compliance KEMA Keur certificate
----------------	---------------------------------------

Energy consumption kWh/1,000 hours	24 kWh
------------------------------------	--------

EPREL Registration Number	1370829
---------------------------	---------

CE mark	Yes
---------	-----

EU RoHS compliant	Yes
-------------------	-----

Flickering value (PstLM)	1
--------------------------	---

Stroboscopic effect	0.4
---------------------	-----

Ambient temperature range	-20°C to 45°C
---------------------------	---------------

Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	CorePro LED PLL Mains 24W 830 4P
--------------------	----------------------------------

Full product name	CorePro LED PLL Mains 24W 830 4P
-------------------	----------------------------------

Full EOC	872016915711800
----------	-----------------

Order code	929003592802
------------	--------------

Material no. (12 NC)	929003592802
----------------------	--------------


Numerator – quantity per pack	1
-------------------------------	---

EAN/UPC – Product/Case	8720169157118
------------------------	---------------

Numerator – packs per outer box	10
---------------------------------	----

EAN/UPC - Case	8720169157125
----------------	---------------



Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLL Mains 24W 830 4P	17 mm	38 mm	453 mm	528 mm	535 mm


CorePro LED PLL

Photometric data



Spectral Power Distribution Colour - CorePro LED PLL Mains 24W 830 4P


Light Distribution Diagram - CorePro LED PLL Mains 24W 830 4P




General Uniform Lighting - CorePro LED PLL Mains 24W 830 4P

General uniform lighting - CorePro LED PLL Mains 24W 830 4P

Lifetime



Life Expectancy Diagram



LifetimeVsTc

CorePro LED PLL

Lifetime



Lumen Maintenance Diagram - CorePro LED PLL Mains 24W 830 4P

FailureRate



Lumen Maintenance Diagram - CorePro LED PLL Mains 24W 830 4P

