



LED BR30

8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT

Contractor grade, LEDbulb, BR30, 65 W, E26, 5000 K, 650 lm, 15000 hour(s), Plastic

Contractor grade, LEDbulb, BR30, 65 W, E26, 5000 K, 650 lm, 15000 hour(s), Plastic, 73 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	110 degree(s)
Luminous Flux	650 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	73 lm/W
Color Consistency	6DSCM
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8.8 W


Lamp Current (Nom)	90 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
UL Type	Yes
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	BR30
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.148 lb

LED BR30

Approval and Application	
EU RoHS compliant	Yes
T20 compliant	No
Ambient temperature range	-4 °F to 113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Product Data	
Order product name	8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT



Full product name	8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT
Order code	583617
Material Nr. (12NC)	929003620104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677583613
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677583618

Dimensional drawing



Product	D	C
8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT	3-3/4 inch	5-1/8 inch

Photometric data




General uniform lighting - 8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT

Spectral Power Distribution Colour - 8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT

LED BR30

Photometric data




Light Distribution Diagram - 8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT

