



MASTER LEDspot GU10 UltraEfficient

MAS LEDspot UE 2.1-50W GU10 ND 827 EELA

With Philips Ultra Efficient GU10 LED spots, you have the perfect retrofit lamp to help your customers save energy and money with high quality, long-lasting and ultra energy-efficient LED.

Product data

General Information	
Cap base	GU10
Nominal lifetime	50,000 h
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
Light Technical	
Colour Code	827 [CCT of 2700K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	375 lm
Luminous intensity (nom.)	680 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	178 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	375 lm
Photobiological safety according to EN 62471 RG1	


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	2.1 W
Lamp current (nom.)	21 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb material	Glass
Bulb shape	PAR16

MASTER LEDspot GU10 UltraEfficient

Net Weight (Piece)	0.052 kg
Approval and Application	
Energy Efficiency Class	A
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	3 kWh
EPREL Registration Number	1428242
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20 to +45 °C
Application Conditions	
Can it be used in closed luminaires	No



Product Data	
Order product name	MAS LEDspot UE 2.1-50W GU10 ND 827 EELA
Full product name	MAS LEDspot UE 2.1-50W GU10 ND 827 EELA
Full EOC	872016919485400
Order code	19485400
Material no. (12 NC)	929003634602
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169194854
Numerator – packs per outer box	10
EAN/UPC – Case	8720169194861

Dimensional drawing



Product	D	C
MAS LEDspot UE 2.1-50W GU10 ND 827 EELA	50 mm	54 mm

Photometric data




Accent Lighting Spots - MAS LEDspot UE 2.1-50W GU10 ND 827 EELA

Light Distribution Diagram - MAS LEDspot UE 2.1-50W GU10 ND 827 EELA


MASTER LEDspot GU10 UltraEfficient

Photometric data




Spectral Power Distribution Colour - MAS LEDspot UE 2.1-50W GU10 ND 827
EELA

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDspot UE 2.1-50W GU10 ND 827
EELA

