



MASTER LED tube Mains T5

MAS LEDtube 600mm HO 10.5W 840 T5

MASTER, LEDtube, T5, Mains, 23-5/8 inch, 10.5 W, 24W TL5 HO, 4000 K, 1600 lm, CRI 80, 60000 hour(s)

MASTER, LEDtube, T5, Mains, 23-5/8 inch, 10.5 W, LED alternative to 24W TL5 HO, 4000 K, 1600 lm, CRI 80, 60000 hour(s), 152 lm/W, EEL D, G5, Beam angle 200 degree(s), Glass, 600 mm, RGO, SDCM 6, PF 0.92, IP20, SVM 0.4, PstLM 1

Product data

General Information	
Cap-Base	G5
Nominal lifetime	60,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LEDtube
Flux measurement reference	Sphere
Warranty period	5 years
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,600 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	152 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Photobiological safety according to EN 62471	RGO
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10.5 W
Lamp Current (Max)	47 mA
Lamp Current (Min)	47 mA
Lamp Current (Nom)	47 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.92
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	24W TL5 HO
Inrush current at mains	7
Max. lamp no. on MCB B type 10A - Mains	100
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-

MASTER LED tube Mains T5

Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – Mains	159
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-
Ballast Compatibility	Mains

Temperature

T-Case Maximum (Nom)	140 °F
----------------------	--------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	23-5/8 inch
Bulb Shape	T5
Net Weight (Piece)	0.176 lb

Approval and Application

Energy Efficiency Class	D
Energy Saving Product	Yes
Approval Marks	RoHS compliance

Energy Consumption kWh/1000 h	11 kWh
EPREL Registration Number	1590872
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-4 to +113 °F


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	MAS LEDtube 600mm HO 10.5W 840 T5
Full product name	MAS LEDtube 600mm HO 10.5W 840 T5
Full product code	872016927531700
Order code	929003734402
Material Nr. (12NC)	929003734402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169275317
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169275324


Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 600mm HO 10.5W 840 T5		3/4 inch	21-5/8 inch	21-15/16 inch	22-3/16 inch

MASTER LED tube Mains T5


Photometric data



Light Distribution Diagram - MAS LEDtube 600mm HO 10.5W 840 T5




Spectral Power Distribution Colour - MAS LEDtube 600mm HO 10.5W 840 T5




General Uniform Lighting
1 x T5 LED 10.5W HO 10.5W 840 T5
Page 1/1

General uniform lighting - MAS LEDtube 600mm HO 10.5W 840 T5

Lifetime





Lumen Maintenance Diagram - MAS LEDtube 600mm HO 10.5W 840 T5



Life Expectancy Diagram


MASTER LED tube Mains T5

Lifetime



LifetimeVsTc

FailureRate



Lumen Maintenance Diagram - MAS LEDtube 600mm HO 10.5W 840 T5

